

NEW OLED MONO Automatic Injector



The Perfect Solution for All Your Injecting Needs

MONO Equipment's NEW Automatic Injector is based on its much-loved predecessor, the Auto Jammer, which is still used by one of the USA's top doughnut chains.

Our latest injector model has been updated to feature a 65k full-colour OLED screen which contains a wealth of new features, including icon-driven menus and the ability to be able to pre programme the speed, duration and suckback values for each individual injection programme; this ensures the exact volume of filling is injected each and every time.

The generous 9.1kg hopper can be changed simply and easily, giving you the flexibility to quickly change between fillings for different types of product. Simply order additional hoppers when you purchase the Automatic Injector.

The range of Injector Needles has also been extended to include a new 4-Prong Needle which has been specially designed for injecting filling into ring doughnuts.





The NEW full-colour OLED Control Panel featured on the Automatic Injector provides a very simple, intuitive and user-friendly interface making both programming and using the Automatic Injector a pleasure. Using just six buttons allows you to control every aspect of the injecting process including speed, duration and suck-



Using the Numerical Menu allows you to store up to 99 programmes for instant recall.



Using the *Icon Menu* allows you to scroll through a pre-loaded selection of fruit and fillings for quick and easy



Using the Manual Mode allows you to create a one-off injection programme without having to save it for future use.



Using Continuous Mode allows you to deliver a continuous flow of filling until stopped. This can also be used to empty the hopper and gears.



The Guest Mode allows you to set up a programme for a 'guest' product which may be used for a short period of time e.g. a promotion.



The Time setting allows you to programme the number of seconds that the filling is injected into the product.



The Speed setting allows you to programme the speed (rpm) at which the filling is injected into the product.



The Suckback setting allows you to programme the number of seconds of suckback to create a clean finish and reduce wastage.



The Order setting allows you to re-order the pictorial icons so that your favourites are at the start of the list.



NEW OLED MONO Automatic Injector

Accessories:



Hoppers Ideal for holding different fillings for quick change over. Code: 053-02-00000



4-Prona Needles Specially designed for injecting ring dounguts in 4 places.

Code: 053-03-04000 (needles) Code: 053-03-05000 (red caps)



Standard Needles Standard and elongated needles

Code: 053-03-03900 (8mm diam) Code: 053-03-04700 (114mm diam)



Activating Foot Pedal Used instead of the Activating Tray for easier switch control.

Code: B842-07-039

Power Supply Leads:



British Power Supply Lead Code: B842-06-037



European Power Supply Lead Code: B842-06-038



American Power Supply Lead Code: B842-06-039



Japanese Power Supply Lead

Code: B842-06-040 + Code: B790-93-001 (PSE)



Australian Supply Lead Code: B842-06-041

Specifications and Dimensions:

Item	Specification
Width (mm)	401
Depth (mm)	304
Height with Hopper (mm)	480.5
Height without Hopper (mm)	212
Weight (kg)	8
Output per Hour (pcs)	1,200
Power Supply	Single phase, 13A maximum load

Noise less than 85dB

Ordering Your MONO OLED Automatic Injector:

When placing your order please ensure you include the following items which suit your particular needs:

- Base Unit(s)
- Your chosen Standard Needles (if required)
- Your 4-Prong ring doughnut Needles (and caps if required)
- Activating Foot Pedal (if required)
- The correct Power Supply for your market